



VF108PM

Small distributor,golf,flush,1row,8M,IP40,MS-terminal,N+PE,white door

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	8
-------------------	---

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	225 mm
Width	275 mm
Depth	97.50 mm
Built-in height	189 mm
Built-in width	242 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	72 mm
----------------	-------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	8
-----------------------	---

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
Impact resistance IK	IK07

Safety

Locking type	Snap on lock
	Without lock
Glow wire test	650 °C

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes