



JK216BSH

#### JK216 Half Width Side Ext Box Glazed

##### Technical Features

###### Installation, mounting

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

###### Electric current

|               |       |
|---------------|-------|
| Rated current | 250 A |
|---------------|-------|

###### Equipment

|                            |     |
|----------------------------|-----|
| With lock                  | No  |
| Has neutral terminal block | Yes |

###### Dimensions

|        |           |
|--------|-----------|
| Height | 1250 mm   |
| Width  | 232.50 mm |
| Depth  | 165.50 mm |

###### Cover, door

|                           |    |
|---------------------------|----|
| Number of cabinet doors   | 1  |
| Door/cover is transparent | No |

###### Materials

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 7035       |
| Colour   | Light grey |

###### Equipment

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
|-----------------------------|-----|

###### Safety

|                               |                                   |
|-------------------------------|-----------------------------------|
| Protection class              | Isolation class III               |
| Impact resistance IK          | IK05                              |
| Ingress Protection (IP) class | IP2XC                             |
| Locking type                  | Quarter turn lock<br>Without lock |

###### Sustainability

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |