



VF108TF2

Small distributor,golf,flush,1row,8M,IP40,MS-terminal,PE,transparent door

**Technical Features**

**Voltage**

Nominal voltage	400 - 400 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Flush mounting

**Electric current**

Rated current	63 A
---------------	------

**Equipment**

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No

**Capacity**

Number of modules	8
-------------------	---

**Functions**

With conduit inlets	Yes
---------------------	-----

**Dimensions**

Height	225 mm
Width	275 mm
Depth	97.50 mm
Built-in height	189 mm
Built-in width	242 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Built-in depth	72 mm
----------------	-------

**Cover, door**

Number of locks	0
-----------------	---

**Dimensions**

Number of width units	8
-----------------------	---

**Cover, door**

Door/cover is transparent	Yes
Cabinet door type	Single door

**Materials**

Material	Plastic
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Materials**

Ultraviolet-resistant	No
-----------------------	----

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07

---

**Safety**

Locking type	Snap on lock Without lock
Glow wire test	650 °C
Protection class with door	IP40

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes