



936712509



Push-button, NO contact, screw terminals, Integro - Design Flow/Pure, pol wh gl

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Single rocker
Number of poles	1

Materials

Colour	Polar white
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated
Transparent	No

Dimensions

Height	55.50 mm
Width	55.50 mm
Depth	25 mm
Built-in depth	10 mm
Built-in depth flush-mounted boxes	13 mm

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Safety

Ingress Protection (IP) class	IP44
-------------------------------	------

Accessories

Has labelling field	No
---------------------	----

Texts

Imprint	Without imprint
Type of connection	With screw terminals

Suitable for

integro	
---------	--

Sustainability

RoHS conform	Yes
--------------	-----