



FWB71S

FWB encl.,univers,7-rows 84 modules cl.II IP44 w plain door, 1100x300x161mm,QC

**Technical Features**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	125 A
---------------	-------

**Equipment**

Number of rails	7
Number of rows	7
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

**Capacity**

Number of modules	84
-------------------	----

**Functions**

Has protection main switch	No
With conduit inlets	Yes

**Dimensions**

Height	1100 mm
Width	300 mm
Depth	165 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Built-in depth	161 mm
----------------	--------

**Cover, door**

Number of locks	1
-----------------	---

**Dimensions**

Number of width units	12
-----------------------	----

**Cover, door**

Type of handle	Hinged pattern handle
Door/cover is transparent	No

**Connection**

Number of conduit inlets	4
--------------------------	---

**Connectivity**

Mounting type	Surface mounting
---------------	------------------

**Materials**

Material	Steel
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP44

**Safety**

Locking type	Without lock
Glow wire test	750 °C

**Sustainability**

RoHS conform	Yes
--------------	-----