



FWB73S

**FWB encl.,univers,7-rows 252 modules cl.II IP44 w.plain door, 1100x800x161mm,QC**

**Technical Features**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	125 A
---------------	-------

**Equipment**

Number of rails	21
Number of rows	0
Number of section in width	3
With lock	No
Has neutral terminal block	Yes

**Capacity**

Number of modules	252
-------------------	-----

**Functions**

Has protection main switch	No
With conduit inlets	Yes

**Dimensions**

Height	1100 mm
Width	800 mm
Depth	165 mm
Built-in height	1100 mm
Built-in width	800 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Built-in depth	161 mm
----------------	--------

**Cover, door**

Number of locks	1
-----------------	---

**Dimensions**

Number of width units	36
-----------------------	----

**Cover, door**

Type of handle	Hinged pattern handle
Door/cover is transparent	No

**Connection**

Number of conduit inlets	12
--------------------------	----

**Connectivity**

Mounting type	Surface mounting
---------------	------------------

**Materials**

Material	Steel
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Materials**

Ultraviolet-resistant	No
-----------------------	----

---

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP44
Locking type	Without lock
Glow wire test	750 °C

**Sustainability**

---

RoHS conform	Yes
--------------	-----