



FWB73S

FWB encl.,univers,7-rows 252 modules cl.II IP44 w.plain door, 1100x800x161mm,QC

### Technical Features

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

#### Electric current

Rated current	125 A
---------------	-------

#### Equipment

Number of rails	21
Number of rows	7
Number of section in width	3
With lock	No
Has neutral terminal block	Yes

#### Capacity

Number of modules	252
-------------------	-----

#### Functions

Has protection main switch	No
With conduit inlets	Yes

#### Dimensions

Height	1100 mm
Width	800 mm
Depth	165 mm
Built-in height	1100 mm
Built-in width	800 mm

#### Cover, door

Number of cabinet doors	1
-------------------------	---

#### Dimensions

Built-in depth	161 mm
----------------	--------

#### Cover, door

Number of locks	1
-----------------	---

#### Dimensions

Number of width units	36
-----------------------	----

#### Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No

#### Connection

Number of conduit inlets	12
--------------------------	----

#### Connectivity

Mounting type	Surface mounting
---------------	------------------

#### Materials

Material	Steel
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

#### Materials

Ultraviolet-resistant	No
-----------------------	----

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP44
Locking type	Without lock
Glow wire test	750 °C

**Sustainability**

RoHS conform	Yes
--------------	-----