



FWB74S

FWB encl.,univers,7-rows 336 modules cl.II IP44 w.plain door, 1100x1050x161mm,QC

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rails	28
Number of rows	0
Number of section in width	4
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	336
-------------------	-----

Functions

Has protection main switch	No
With conduit inlets	Yes

Dimensions

Height	1100 mm
Width	1050 mm
Depth	165 mm
Built-in height	1100 mm
Built-in width	1050 mm

Cover, door

Number of cabinet doors	2
-------------------------	---

Dimensions

Built-in depth	0 mm
----------------	------

Cover, door

Number of locks	1
-----------------	---

Dimensions

Number of width units	48
-----------------------	----

Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No

Connection

Number of conduit inlets	16
--------------------------	----

Connectivity

Mounting type	Surface mounting
---------------	------------------

Materials

Material	Steel
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP44
Locking type	Without lock
Glow wire test	750 °C

Sustainability

RoHS conform	Yes
--------------	-----