



JK208BG

**250A 16 Way TPN Board Glazed Door**

**Technical Features**

**Installation, mounting**

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 250 A |
|---------------|-------|

**Equipment**

|                            |     |
|----------------------------|-----|
| With lock                  | Yes |
| Has neutral terminal block | Yes |

**Dimensions**

|        |           |
|--------|-----------|
| Height | 1250 mm   |
| Width  | 465 mm    |
| Depth  | 165.50 mm |

**Cover, door**

|                           |    |
|---------------------------|----|
| Number of cabinet doors   | 1  |
| Door/cover is transparent | No |

**Materials**

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 7035       |
| Colour   | Light grey |

**Equipment**

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
|-----------------------------|-----|

**Safety**

|                               |                               |
|-------------------------------|-------------------------------|
| Protection class              | Isolation class III           |
| Impact resistance IK          | IK05                          |
| Ingress Protection (IP) class | IP30                          |
| Locking type                  | Key lock<br>Quarter turn lock |

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |