



VF218PT2

Small distributor,golf,flush,2row,36M,IP40,MS-terminal,ANZ,N+PE,white door

Technical Features

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Flush mounting

Electric current

Rated current 80 A

Equipment

Number of rails 2

Number of rows 2

Number of section in width 1

With lock No

Has neutral terminal block Yes

Capacity

Number of modules 36

Functions

With conduit inlets Yes

Dimensions

Height 418 mm

Width 460 mm

Depth 97.50 mm

Built-in height 382 mm

Built-in width 426 mm

Cover, door

Number of cabinet doors 1

Dimensions

Built-in depth 72 mm

Cover, door

Number of locks 0

Dimensions

Number of width units 18

Cover, door

Door/cover is transparent No

Cabinet door type Single door

Materials

Material Plastic

RAL code 9010

Colour Pure white

Equipment

Has earthing terminal block Yes

Has mounting plate No

Materials

Ultraviolet-resistant No

Safety

Protection class Isolation class II

Impact resistance IK IK07

Safety

Ingress Protection (IP) class	IP40
Locking type	Snap on lock Without lock
Glow wire test	850 °C
Protection class with door	IP40

Sustainability

RoHS conform	Yes
--------------	-----