



VML1010

Design 10, Dual Row, 6+10 Way HI 63A Sw 2*63A 30mA RCCB Type A SPD

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Architecture

Number of poles	2
-----------------	---

Functions

Overvoltage protection	Yes
------------------------	-----

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth	100 mm
Height	486 mm
Width	299 mm
Thickness of sidewall	0.90 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	9010
Colour	Pure white
Material	Steel

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of RCCB in enclosure	2
-----------------------------	---

Equipment

Number of rows	2
Number of rails	2
Extension possible	No
With bell transformer	No
With socket outlet	No

Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC

Compatibility

Cooker group suitable as power current group	No
--	----