



WS012



Systo 1M 2W switch

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Pure white
RAL code	9010
Surface finish	Matt Satin finish
Material	Polycarbonate (PC)

Identification

Assembly arrangement	Mechanism with upper casing
----------------------	-----------------------------

Connectivity

Mounting type	Clamp mounting Recessed
---------------	----------------------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	45 x 22 mm
Built-in depth	40 mm
Built-in depth flush-mounted boxes	40 mm

Safety

Ingress Protection (IP) class	IP31D
Impact resistance IK	IK07

Electric current

Rated current	10 A
---------------	------

Connection

Type of contacts	2-way
------------------	-------

Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way