



16357103

**Centre plate for mechanical timer, K.5, al., al. anodised**

**Technical Features**

**Architecture**

|                           |          |
|---------------------------|----------|
| Control/operation element | Rotative |
|---------------------------|----------|

**Materials**

|                |           |
|----------------|-----------|
| Colour         | Aluminium |
| RAL code       | 9006      |
| Surface finish | Matt      |
| Material       | Aluminium |
| Treatment      | Anodised  |

**Dimensions**

|        |          |
|--------|----------|
| Height | 56.10 mm |
| Width  | 70.50 mm |
| Depth  | 22 mm    |

**Connectivity**

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

**Equipment**

|                                |    |
|--------------------------------|----|
| Monitoring window/light outlet | No |
|--------------------------------|----|

**Accessories**

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Texts**

|                   |                                |
|-------------------|--------------------------------|
| Imprint           | With time scale symbol imprint |
| Installation mode | For screw fastening            |

**Identification**

|                      |                     |
|----------------------|---------------------|
| Assembly arrangement | Central cover plate |
|----------------------|---------------------|

**Suitable for**

|     |  |
|-----|--|
| K.x |  |
|-----|--|

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |