



47693502



WATERPROOF - COMPLETE PRODUCT - SCHUKO SOCKET WITH CP WITH FPL AND KEY

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Use conditions

Operating temperature -15 - 30 °C

Frequency

Frequency 50 - 50 Hz

Materials

Colour Polar white
RAL code 9010
Surface finish Matt
Material Thermoplastic
Treatment Untreated

Dimensions

Height 76 mm
Width 76 mm
Depth 65 mm
Built-in depth flush-mounted boxes 0 mm

Connection

Connector/plug type Plug-in terminal
Conductor cross-section 1.0 - 2.5 mm²

Installation, mounting

Mounting on Surface mounting

Connectivity

Type of connection Plug-in connection
Mounting type Screw mounting

Equipment

Connector/plug type socket outlet SCHUKO
Rotated central insert No
With hinged lid Yes
With round protective earth pin No
With signal lamp No
With lock Yes

Accessories

Has labelling field Yes

Cover, door

Type of lid Self-closing hinged cover, can be arrested in end position

Capacity

Number of modules 1

Safety

With enhanced contact protection No
Impact resistance IK IK05
Ingress Protection (IP) class IP55

Functions

With orientation lighting No
With function lighting No

Identification

With imprint	No
--------------	----

Texts

Cover	Complete housing
-------	------------------

Protection	Enhanced contact protection
------------	-----------------------------

Type of connection	With plug-in terminals
--------------------	------------------------

Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor
----------	--

Sustainability

Halogen free	Yes
--------------	-----

RoHS conform	Yes
--------------	-----
