



47693502



**WATERPROOF - COMPLETE PRODUCT - SCHUKO SOCKET WITH CP WITH FPL AND KEY**

**Technical Features**

**Electric current**

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

**Voltage**

|                 |             |
|-----------------|-------------|
| Rated voltage   | 250 V       |
| Nominal voltage | 250 - 250 V |

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -15 - 30 °C |
|-----------------------|-------------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

**Materials**

|                |               |
|----------------|---------------|
| Colour         | Polar white   |
| RAL code       | 9010          |
| Surface finish | Matt          |
| Material       | Thermoplastic |
| Treatment      | Untreated     |

**Dimensions**

|                                    |       |
|------------------------------------|-------|
| Height                             | 76 mm |
| Width                              | 76 mm |
| Depth                              | 65 mm |
| Built-in depth flush-mounted boxes | 0 mm  |

**Connection**

|                         |                           |
|-------------------------|---------------------------|
| Connector/plug type     | Plug clamp                |
| Conductor cross-section | 1.0 - 2.5 mm <sup>2</sup> |

**Installation, mounting**

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

**Connectivity**

|                    |                    |
|--------------------|--------------------|
| Type of connection | Plug-in connection |
| Mounting type      | Screw mounting     |

**Equipment**

|                                   |        |
|-----------------------------------|--------|
| Connector/plug type socket outlet | SCHUKO |
| Rotated central insert            | No     |
| With hinged lid                   | Yes    |
| With round protective earth pin   | No     |
| With signal lamp                  | No     |
| With lock                         | Yes    |

**Accessories**

|                     |     |
|---------------------|-----|
| Has labelling field | Yes |
|---------------------|-----|

**Cover, door**

|             |  |
|-------------|--|
| Type of lid | Self-closing hinged cover, can be arrested in end position |
|-------------|--|

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

**Safety**

|                                  |      |
|----------------------------------|------|
| With enhanced contact protection | No   |
| Impact resistance IK             | IK05 |
| Ingress Protection (IP) class    | IP55 |

|                           |  |                             |
|---------------------------|--|-----------------------------|
| <b>Functions</b>          |  |                             |
| With orientation lighting |  | No                          |
| With function lighting    |  | No                          |
| <b>Texts</b>              |  |                             |
| Imprint                   |  | Without imprint             |
| Cover                     |  | Complete housing            |
| Protection                |  | Enhanced contact protection |
| Type of connection        |  | With plug-in terminals      |
| <b>Sustainability</b>     |  |                             |
| Halogen free              |  | Yes                         |
| RoHS conform              |  | Yes                         |