



KDN451D



**Insulated busbar 3x(P+N) 80A fork 16mm<sup>2</sup> 12M**

**Technical Features**

**Electric current**

Rated current 80 A

**Architecture**

Number of poles 4

**Dimensions**

Length 215 mm

**Voltage**

Rated impulse withstand voltage Uimp 4000 V

Rated operational voltage Ue 230 - 400 V

**Connection**

Cross-section rigid conductor 16 mm<sup>2</sup>

Connector/plug type Phase busbar with fork

**Use conditions**

Operating temperature -25 - 55 °C

**Capacity**

Number of modules 12

**Sustainability**

RoHS conform Yes