



KDN451D



Insulated busbar 3x(P+N) 80A fork 16mm<sup>2</sup> 12M

Technical Features

Electric current

Rated current	80 A
---------------	------

Architecture

Number of poles	4
-----------------	---

Dimensions

Length	215 mm
--------	--------

Voltage

Rated impulse withstand voltage Uimp	4000 V
Rated operational voltage Ue	230 - 400 V

Connection

Cross-section rigid conductor	16 mm <sup>2</sup>
Connector/plug type	Phase busbar with fork

Use conditions

Operating temperature	-25 - 55 °C
-----------------------	-------------

Capacity

Number of modules	12
-------------------	----

Sustainability

RoHS conform	Yes
--------------	-----