



KDN451D



Insulated busbar 3x(P+N) 80A fork 16mm² 12M

Technical Features

Electric current

Rated current 80 A

Architecture

Number of poles 4

Dimensions

Length 215 mm

Voltage

Rated impulse withstand voltage Uimp 4000 V

Rated operational voltage Ue 230 - 400 V

Connection

Cross-section rigid conductor 16 mm²

Connector/plug type Phase busbar with fork

Use conditions

Operating temperature -25 - 55 °C

Capacity

Number of modules 12

Sustainability

RoHS conform Yes