



KDN451E

Insulated busbar 3x(P+N) 80A fork 16mm² 54M

Technical Features

<b>Electric current</b>	
Rated current	80 A
<b>Architecture</b>	
Number of poles	4
<b>Dimensions</b>	
Length	1000 mm
<b>Voltage</b>	
Rated impulse withstand voltage Uimp	4500 V
Rated operational voltage Ue	230 - 400 V
<b>Connection</b>	
Cross-section rigid conductor	16 mm²
Connector/plug type	Phase busbar with fork
<b>Capacity</b>	
Number of modules	54
<b>Sustainability</b>	
Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes