



KXA02LH

Feed-through terminal -phase , 2,5mm², 800V-24A, screw connection

Technical Features

Electric current

| | |
|---------------|------|
| Rated current | 24 A |
|---------------|------|

Dimensions

| | |
|--------|----------|
| Height | 48.50 mm |
| Width | 44.50 mm |
| Depth | 5 mm |

Installation, mounting

| | |
|-------------|----------|
| Mounting on | DIN rail |
|-------------|----------|

Connection

| | |
|----------------------------------|---------------------------|
| Cross-section flexible conductor | 0.5 - 2.5 mm ² |
| Cross-section rigid conductor | 0.5 - 4 mm ² |

Materials

| | |
|----------|----------------|
| Colour | Grey |
| Material | Polyamide (PA) |

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |