



WGDS110US

**10A 2 pin switched socket**

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Output current	0 mA
Rated current	10 A

**Voltage**

Output voltage	0-0 V
----------------	-------

**Use conditions**

Operating temperature	-20 - 45 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Power**

Output power	0 W
Power consumption standby	0 W

**Materials**

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated
Contains recycled material (% of total plastic weight)	0 %

**Dimensions**

Height	30 mm
Width	86 mm
Depth	20 mm

**Cable**

Cable length	0 m
--------------	-----

**Dimensions**

Built-in depth flush-mounted boxes	35 mm
Built-in depth	20 mm

**Connection**

Connector/plug type	British Standard
Cross-section flexible conductor without wire end sleeve	0,08 - 4 mm <sup>2</sup>
Number of conduit inlets	0

**Installation, mounting**

Mounting on	Flush mounting
Mounting-/Connection Position	Back

**Connectivity**

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting
Connector/plug type USB	British Standard

**Equipment**

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

---

**Equipment**

---

With lock	No
-----------	----

---

**Accessories**

---

Has labelling field	No
---------------------	----

---

Pre-equipped with	None
-------------------	------

---

**Capacity**

---

Number of modules	0
-------------------	---

---

**Safety**

---

With enhanced contact protection	No
----------------------------------	----

---

Impact resistance IK	IK02
----------------------	------

---

Ingress Protection (IP) class	IP20
-------------------------------	------

---

**Functions**

---

With orientation lighting	No
---------------------------	----

---

With function lighting	No
------------------------	----

---

**Identification**

---

With imprint	No
--------------	----

---

**Suitable for**

---

shark	
-------	--

---

**Sustainability**

---

Halogen free	Yes
--------------	-----

---