



WGDS110US

## 10A 2 pin switched socket

### Technical Features

#### Electric current

Rated current	10 A
Output current	0 mA

#### Voltage

Rated voltage	250 V
Nominal voltage	220-250 V
Output voltage	0-0 V

#### Use conditions

Operating temperature	-20-45 °C
-----------------------	-----------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Power

Output power	0 W
Power consumption standby	0 W

#### Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated
Contains recycled material (% of total plastic weight)	0 %

#### Dimensions

Height	30 mm
Width	86 mm
Depth	20 mm
Built-in depth flush-mounted boxes	35 mm
Built-in depth	20 mm

#### Connection

Connector/plug type	British Standard
Cross-section flexible conductor without wire end sleeve	0.08 - 4 mm <sup>2</sup>

#### Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Back

#### Connectivity

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting
Connector/plug type USB	British Standard

#### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

#### Accessories

Has labelling field	No
Pre-equipped with	None

Product Datasheet

WGDS110US

<b>Capacity</b>	
Number of modules	0
<b>Safety</b>	
With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20
<b>Functions</b>	
With orientation lighting	No
With function lighting	No
<b>Identification</b>	
With imprint	No
<b>Suitable for</b>	
shark	
<b>Sustainability</b>	
Halogen free	Yes