



75144830



**IP20**

**KNX glass sensor 4gang comf, intg bus coupl. unit, KNX-TS sensor, glass p.white**

### Technical Features

#### Installation, mounting

Mounting on Flush mounting

#### Use conditions

Operating temperature -5 - 45 °C

#### Functions

With room temperature controller Yes

#### Power

Current consumption 12.50 mA

#### Dimensions

Built-in depth 24.20 mm

Built-in depth flush-mounted boxes 27 mm

Height 160 mm

Width 86 mm

Depth 37.70 mm

#### Equipment

Number of actuation points 8

#### Controls and indicators

With LED indication Yes

#### Materials

Colour Polar white

RAL code 9010

Material Glass

Surface finish Glossy

#### Accessories

Has labelling field No

#### Screen

With display No

#### Texts

Function For switch, push-button, dimmer and shutter functions  
Blocking function for sensor surface e.g. for cleaning the glass surface

Installation mode For vertical mounting

Temperature Additional connection for external temperature sensor  
Integrated temperature sensor for operation as controller extension unit  
Temperature measurement via internal Temperature sensor or external communication object

#### Sustainability

REACH-SVHC free Yes

RoHS conform Yes