




75144835



IP20

KNX glass sensor 4gang comf, intg bus coupling unit, KNX-TS sensor, glass black

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Functions

With room temperature controller	Yes
----------------------------------	-----

Power

Current consumption	12.50 mA
---------------------	----------

Dimensions

Built-in depth	24.20 mm
Built-in depth flush-mounted boxes	27 mm
Height	160 mm
Width	86 mm
Depth	37.70 mm

Equipment

Number of actuation points	8
----------------------------	---

Controls and indicators

With LED indication	Yes
---------------------	-----

Materials

Colour	Black
RAL code	9005
Material	Glass
Surface finish	Glossy

Accessories

Has labelling field	No
---------------------	----

Screen

With display	No
--------------	----

Texts

Function	For switch, push-button, dimmer and shutter functions Blocking function for sensor surface e.g. for cleaning the glass surface
Installation mode	For vertical mounting
Temperature	Additional connection for external temperature sensor Integrated temperature sensor for operation as controller extension unit Temperature measurement via internal Temperature sensor or external communication object

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes