



EH111



IP20



**Time switch daily cycle with reserve 3 modules**

**Technical Features**

**Equipment**

Number of channels 1

**Frequency**

Frequency 50 - 50 Hz

**Power**

Power consumption during operation 0.50 VA

230 V incandescent and halogen lamp 900 W

Power incandescent lamp 900 - 900 W

**Functions**

Number of function channels 1

**Connection**

Number of contacts 1

Cross-section flexible conductor 1 - 4 mm<sup>2</sup>

Cross-section rigid conductor 1 - 4 mm<sup>2</sup>

**Use conditions**

Operating temperature -10 - 45 °C

**Capacity**

Number of modules 3

**Dimensions**

Height 90 mm

Width 54 mm

Depth 60 mm

**Texts**

Switch mode Change-over contact, usable as NC or NO

Installation mode For mounting on DIN rail

**Electric current**

Max. power (cos phi 0,6) 3 A

**Endurance**

Electrical durability at nominal load in AC1 in operating cycles 50000

**Texts**

Type of connection With screw terminals

**Voltage**

Rated operational voltage Ue 230 - 230 V

**Power**

Power loss at full load 1 W

**Settings**

Programme cycles Programme cycle: 24 hours

**Lighting**

LED lamp power 450 W

**Sustainability**

RoHS conform Yes