



EH111



IP20



Time switch daily cycle with reserve 3 modules

Technical Features

Equipment

Number of channels	1
--------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

Power consumption during operation	0.50 VA
230 V incandescent and halogen lamp	900 W
Power incandescent lamp	900 - 900 W

Functions

Number of function channels	1
-----------------------------	---

Connection

Number of contacts	1
Cross-section flexible conductor	1 - 4 mm ²
Cross-section rigid conductor	1 - 4 mm ²

Use conditions

Operating temperature	-10 - 45 °C
-----------------------	-------------

Capacity

Number of modules	3
-------------------	---

Dimensions

Height	90 mm
Width	54 mm
Depth	60 mm

Texts

Switch mode	Change-over contact, usable as NC or NO
Installation mode	For mounting on DIN rail

Electric current

Max. power (cos phi 0,6)	3 A
--------------------------	-----

Endurance

Electrical durability at nominal load in AC1 in operating cycles	50000
--	-------

Texts

Type of connection	With screw terminals
--------------------	----------------------

Voltage

Rated operational voltage Ue	230 - 230 V
------------------------------	-------------

Power

Power loss at full load	1 W
-------------------------	-----

Settings

Programme cycles	Programme cycle: 24 hours
------------------	---------------------------

Lighting

LED lamp power	450 W
----------------	-------

Sustainability

RoHS conform	Yes
--------------	-----