



FP34TN2

Enclosure, univers, IP54,CL1, 500x1050x205mm, empty

Technical Features

Dimensions

| | |
|-----------------------|---------|
| Height | 500 mm |
| Width | 1050 mm |
| Depth | 205 mm |
| Thickness of sidewall | 1 mm |

Safety

| | |
|-------------------------------|--------------------------|
| Ingress Protection (IP) class | IP54 |
| Protection class | Isolation class I |
| Locking type | Bar lock Without lock |
| Impact resistance IK | IK09 |

Equipment

| | |
|---------------------------------|---|
| Number of section in width | 4 |
| Number of flange plate openings | 8 |

Installation, mounting

| | |
|----------------------------|---------------|
| Mounting on | Wall mounting |
| Suitable for outdoor usage | No |

Materials

| | |
|-----------|---------------|
| Colour | Pure white |
| RAL code | 9010 |
| Treatment | Powder coated |
| Material | Steel |

Equipment

| | |
|----------------|---|
| Number of rows | 3 |
|----------------|---|

Materials

| | |
|----------------|------|
| Surface finish | Matt |
|----------------|------|

Cover, door

| | |
|---------------------------|------------------------|
| Number of cabinet doors | 1 |
| Number of locks | 1 |
| Door/cover is transparent | No |
| Cabinet door type | Double door, symmetric |

Electric current

| | |
|---------------|-------|
| Rated current | 250 A |
|---------------|-------|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|