




WNE123

cubyko Triple horizontal socket 2P+E screwless flush mounted grey IP55

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt Satin finish
Material	Polypropylene (PP)

Dimensions

Height	45 mm
Width	135 mm
Depth	42.50 mm
Built-in depth flush-mounted boxes	40 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	French norm NF
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	6
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK07
Ingress Protection (IP) class	IP55

Functions

With orientation lighting	No
---------------------------	----

Texts

Imprint	With imprint
Cover	For covering of socket outlets
Protection	Without protective screen

Suitable for

Hager cubyko	
--------------	--