



75663726



Push-butt. 3gang, w. lab. fields, room therm., displ., Q.x, anthr. velvety

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Functions

With room temperature controller Yes

Dimensions

Built-in depth 21.40 mm

Built-in depth flush-mounted boxes 25 mm

Height 123.20 mm

Width 70.80 mm

Depth 34.80 mm

Equipment

Number of actuation points 8

Controls and indicators

With LED indication Yes

Materials

Colour Anthracite

RAL code 7021

Material Thermoplastic

Surface finish Velvety

Accessories

Has labelling field Yes

Screen

With display Yes

Texts

Function For switch, push-button, dimmer, blind and thermostat functions
With valve protection function

Operating mode Controller operating modes: comfort, standby, night and frost/heat protection mode

Protection With dismantling protection

Temperature Temperature measurement via internal and/or external sensor with mean value formation

Sustainability

REACH-SVHC free Yes

RoHS conform Yes