


75663729



Push-button 3gang, w. labelling fields, room therm., displ., Q.x, pw velvety

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Functions

With room temperature controller Yes

Dimensions

Built-in depth 21.40 mm
 Built-in depth flush-mounted boxes 25 mm
 Height 123.20 mm
 Width 70.80 mm
 Depth 34.80 mm

Equipment

Number of actuation points 8

Controls and indicators

With LED indication Yes

Materials

Colour Polar white
 RAL code 9010
 Material Thermoplastic
 Surface finish Velvety

Accessories

Has labelling field Yes

Screen

With display Yes

Texts

Function For switch, push-button, dimmer, blind and thermostat functions
With valve protection function
 Operating mode Controller operating modes: comfort, standby, night and frost/heat
protection mode
 Protection With dismantling protection
 Temperature Temperature measurement via internal and/or external sensor with
mean value formation

Sustainability

REACH-SVHC free Yes
 RoHS conform Yes