



FP95TN2

enclosure, univers, IP54, CL 1, 1400 x 1300 x 205 mm, exp., empty

**Technical Features**

**Dimensions**

Height	1400 mm
Width	1300 mm
Depth	205 mm
Thickness of sidewall	1 mm

**Safety**

Ingress Protection (IP) class	IP54
Protection class	Isolation class I
Locking type	Bar lock Without lock
Impact resistance IK	IK09

**Equipment**

Number of section in width	5
Number of flange plate openings	10

**Installation, mounting**

Mounting on	Wall mounting
Suitable for outdoor usage	No

**Materials**

Colour	Pure white
RAL code	9010
Treatment	Powder coated
Material	Steel

**Equipment**

Number of rows	9
----------------	---

**Materials**

Surface finish	Matt
----------------	------

**Cover, door**

Number of cabinet doors	2
Number of locks	1
Door/cover is transparent	No
Cabinet door type	Double door, asymmetric

**Electric current**

Rated current	250 A
---------------	-------

**Sustainability**

RoHS conform	Yes
--------------	-----