



451510

Aerial soc. 2hole throughpass soc., 10 dB

Technical Features

Connectivity

Mounting type	Screw mounting
---------------	----------------

Attenuation

Tap loss at 2150 MHz	10.50 dB
Tap loss at 860 MHz	7.50 dB
Through loss 2150 MHz	7 dB
Through loss 860 MHz	4 dB

Connection

Connector/plug type	Pass-through socket
---------------------	---------------------

Frequency

Frequency bandwidth	5 - 2400 MHz
---------------------	--------------

Equipment

Number of outputs	2
-------------------	---

Materials

Material	Metal
----------	-------

Dimensions

Depth	27.20 mm
Built-in depth	40 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes