



451515



Aerial soc. 2hole throughpass soc., 15 dB

Technical Features

Connectivity

Mounting type	Screw mounting
---------------	----------------

Attenuation

Tap loss at 2150 MHz	13.50 dB
Tap loss at 860 MHz	13 dB
Through loss 2150 MHz	2.20 dB
Through loss 860 MHz	1.20 dB

Connection

Connector/plug type	Pass-through socket
---------------------	---------------------

Frequency

Frequency bandwidth	5 - 2400 MHz
Broadband technology	5 - 2400 MHz

Equipment

Number of outputs	2
-------------------	---

Materials

Material	Metal
----------	-------

Dimensions

Depth	27.20 mm
Built-in depth	40 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Texts

Function	Suitable for HDTV
Type of connection	With plug-in terminals
Supporting plate/supporting ring	External eyelets on the supporting ring can be broken off for round designs

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes