



HWX015H

Spring charging motor 380-400V AC 50/60Hz HW2/4 (MO)

Technical Features

Electric current

|               |        |
|---------------|--------|
| Rated current | 0.60 A |
|---------------|--------|

Voltage

|                                           |             |
|-------------------------------------------|-------------|
| Type voltage supply                       | AC          |
| Rated insulation voltage $U_i$            | 450 V       |
| Rated impulse withstand voltage $U_{imp}$ | 6000 V      |
| Command voltage AC                        | 380 - 400 V |

Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -25 - 70 °C |
|-----------------------|-------------|

Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Functions

|                          |    |
|--------------------------|----|
| With auto reset function | No |
|--------------------------|----|

Sustainability

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |