



KDN480A

Insulated busbar 4P 80A fork 16mm² 12M

Technical Features

Electric current

Rated current 80 A

Architecture

Number of poles 4

Dimensions

Length 210 mm

Voltage

Rated impulse withstand voltage U_{imp} 4500 V

Rated operational voltage U_e 230 - 400 V

Connection

Cross-section rigid conductor 16 mm²

Connector/plug type Phase busbar with fork

Capacity

Number of modules 12

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes