



KDN480B

Insulated busbar 4P 80A fork 16mm² 56M

Technical Features

Electric current

Rated current 80 A

Architecture

Number of poles 4

Dimensions

Length 1000 mm

Voltage

Rated impulse withstand voltage Uimp 4500 V

Rated operational voltage Ue 230 - 400 V

Connection

Cross-section rigid conductor 16 mm²

Connector/plug type Phase busbar with fork

Capacity

Number of modules 56

Sustainability

REACH-SVHC free Yes

RoHS conform Yes