



VF104TF

Small distributor,golf,flush,1row,4M,IP40,MS-terminal,PE,transparent door

Technical Features

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Flush mounting

Electric current

Rated current 63 A

Equipment

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block No

Capacity

Number of modules 4

Functions

With conduit inlets Yes

Dimensions

Height 225 mm

Width 204 mm

Depth 97.50 mm

Built-in height 189 mm

Built-in width 170 mm

Cover, door

Number of cabinet doors 1

Dimensions

Built-in depth 72 mm

Cover, door

Number of locks 0

Dimensions

Number of width units 4

Cover, door

Door/cover is transparent Yes

Cabinet door type Single door

Materials

Material Plastic

RAL code 9010

Colour Pure white

Equipment

Has earthing terminal block Yes

Has mounting plate No

Materials

Ultraviolet-resistant No

Safety

Protection class Isolation class II

Impact resistance IK IK07

Safety

Locking type	Snap on lock Without lock
Glow wire test	650 °C
Protection class with door	IP40

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes