



FWB41S

FWB encl.,univers,4-rows 48 modules cl.II IP44 w.plain door, 650x300x161mm,QC

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rails	4
Number of rows	4
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	48
-------------------	----

Functions

Has protection main switch	No
With conduit inlets	Yes

Dimensions

Height	650 mm
Width	300 mm
Depth	165 mm
Built-in height	650 mm
Built-in width	300 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	161 mm
----------------	--------

Cover, door

Number of locks	1
-----------------	---

Dimensions

Number of width units	12
-----------------------	----

Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No
Cabinet door type	Single door

Connection

Number of conduit inlets	4
--------------------------	---

Connectivity

Mounting type	Surface mounting
---------------	------------------

Materials

Material	Steel
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP44
Locking type	Without lock
Glow wire test	750 °C

Sustainability

RoHS conform	Yes
--------------	-----