



FU32AN

Enclosure, NewVegaD, 687x550x182mm, 72 modules, flush-mounted, to complete

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

Electric current

Rated current	160 A
---------------	-------

Equipment

Number of rails	3
Number of rows	3
Number of section in width	2
With lock	No
Has neutral terminal block	No

Capacity

Number of modules	72
-------------------	----

Dimensions

Height	687 mm
Width	600 mm
Depth	182 mm
Built-in width	550 mm
Built-in depth	110 mm
Number of width units	24

Cover, door

Door/cover is transparent	No
Cabinet door type	Single door

Connection

Number of conduit inlets	4
--------------------------	---

Materials

Material	Metal Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	No
Has mounting plate	No

Safety

Protection class	Isolation class II
Ingress Protection (IP) class	IP30
Locking type	Without lock

Sustainability

RoHS conform	Yes
--------------	-----