



M2024

**Divider H: 40 mm**

**Technical Features**

**Dimensions**

Height	40 mm
Length	2000 mm

**Materials**

Material	Polyvinylchloride (PVC)
Treatment	Untreated
Colour	Light grey

**Use conditions**

Operating temperature	-5 - 60 °C
-----------------------	------------

**Connectivity**

Mounting type	Snap-on mounting
---------------	------------------

**Suitable for**

Ceiling pole 45 / Floor pole 45 / LFF 40x60 / LFF 40x90 / LFF 40x110

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes

**Illustrations | Drawings**

