



M2024

Divider H: 40 mm

Technical Features

Dimensions

Height	40 mm
Length	2000 mm

Materials

Material	Polyvinylchloride (PVC)
Treatment	Untreated
Colour	Light grey

Use conditions

Operating temperature	-5 - 60 °C
-----------------------	------------

Connectivity

Mounting type	Snap-on mounting
---------------	------------------

Suitable for

Ceiling pole 45 / Floor pole 45 / LFF 40x60 / LFF 40x90 / LFF 40x110
--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes