



M2026

**partition LF H60**

**Technical Features**

**Dimensions**

Height	60 mm
Length	2000 mm

**Materials**

Material	Polyvinylchloride (PVC)
Treatment	Untreated
Colour	Light grey

**Use conditions**

Operating temperature	-5 - 60 °C
-----------------------	------------

**Connectivity**

Mounting type	Click mounting
---------------	----------------

**Suitable for**

BRP 65x130 / BRP 65x170 / BRP 65x210 / LFF 60x60 / LFF 60x90 / LFF 60x110 / LFF 60x150 / LFF 60x190 / LFF 60x230

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes

**Illustrations | Drawings**

