



M2026

partition LF H60

Technical Features

Dimensions

Height	60 mm
Length	2000 mm

Materials

Material	Polyvinylchloride (PVC)
Treatment	Untreated
Colour	Light grey

Use conditions

Operating temperature	-5 - 60 °C
-----------------------	------------

Connectivity

Mounting type	Click mounting
---------------	----------------

Suitable for

BRP 65x130 / BRP 65x170 / BRP 65x210 / LFF 60x60 / LFF 60x90 / LFF 60x110 / LFF 60x150 / LFF 60x190 / LFF 60x230
--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes