



HEJ630DE

Moulded Case Circuit Breaker h3 x630 TM ADJ 3P3D 630A 70kA FTC

Technical Features

Electric current

Rated current	630 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	100 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	100 kA
Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2	70 kA
Rated current 10°C according to IEC 60947	687.30 A
Rated current 15°C according to IEC 60947	673.40 A
Rated current 20°C according to IEC 60947	659.20 A
Rated current 25°C according to IEC 60947	644.80 A
Rated current 30°C according to IEC 60947	630 A
Rated current at 35°C according to IEC 60947	614.90 A
Rated current at 40°C according to IEC 60947	599.30 A
Rated current 45°C according to IEC 60947	583.40 A
Rated current 50°C according to IEC 60947	567 A
Rated current 55°C according to IEC 60947	550.10 A
Rated current at 60°C according to IEC 60947	532.70 A
Rated current 65°C according to IEC 60947	514.70 A
Rated current 70°C according to IEC 60947	496.10 A

Architecture

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V
Rated operational voltage Ue	220 - 415 V

Functions

Trip unit	TM A/A
-----------	--------

Power

Total power loss under IN	145.2 W
---------------------------	---------

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Settings

Thermal protection knob setting xIN	0.63 0.8 1
-------------------------------------	------------------

Cable

Cable material	Copper Aluminium
----------------	---------------------

Compatibility

Compatible with RDC AOB	Yes
Suitable for DIN Rail	No
Suitable for distribution board	Yes

Dimensions

Dimensions	260 x 140 mm
Height	260 mm
Width	140 mm
Depth	150 mm
Downstream busbar: width, height, diameter screw (max.)	10 mm
	12 mm
	32 mm
Top stream busbar: width, height, diameter screw (max.)	10 mm
	12 mm
	32 mm

Installation, mounting

Mounting-/Connection Position	Front
Nominal tightening torque	18 - 18 Nm
Nominal tightening torque down terminal	18 - 18 Nm
Nominal tightening torque top terminal	18 - 18 Nm

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes