



FD22AN

Enclosure, NewVegaD, 450x550x193mm, 48 modules, surface-mounted, to complete

Technical Features

Dimensions

Height	450 mm
Width	550 mm
Depth	193 mm
Thickness of sidewall	1 mm

Safety

Ingress Protection (IP) class	IP30
Protection class	Isolation class II
Locking type	Without lock

Equipment

Number of flange plate openings	2
---------------------------------	---

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No

Materials

Colour	Pure white
RAL code	9010
Treatment	Powder coated
Material	Metal Plastic

Equipment

Number of rows	2
----------------	---

Cover, door

Number of cabinet doors	0
Number of locks	0
Door/cover is transparent	No

Electric current

Rated current	160 A
---------------	-------

Voltage

Nominal voltage	230 - 400 V
-----------------	-------------

Sustainability

RoHS conform	Yes
--------------	-----