



REN410X



**AUDIO module built-in 2-wire stainless steel matt modesta**

**Technical Features**

**Connectivity**

Mounting type	Built in installation
---------------	-----------------------

**Materials**

Surface finish	Matt
Material	Metal Stainless steel

**Controls and indicators**

Number of call buttons	0
------------------------	---

**Voltage**

Operating voltage	24 - 24 V
-------------------	-----------

**Dimensions**

Dimensions	120 x 120 mm
Height	120 mm
Width	120 mm
Depth	21 mm

**Use conditions**

Operating temperature	-20 - 55 °C
Storage/transport temperature	-30 - 80 °C

**Compatibility**

Installation technique for door communication	2-wire
---	--------

**Connection**

Conductor cross-section	0 - 0 mm <sup>2</sup>
-------------------------	-----------------------

**Equipment**

Modular construction	Yes
----------------------	-----

**Texts**

Installation mode	Installation in surface-mounted or flush-mounted housings
Junction	Pluggable connection terminal block with screw terminals Connection for module Connecting cable
Protection	Loudspeaker and microphone protected against sabotage