



SK604

Changeover switch 4DIRo

Technical Features

Electric current

| | |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

Capacity

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10 - 40 °C |
| Storage/transport temperature | -40 - 80 °C |

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

Connection

| | |
|----------------------------------|--------------------------|
| Cross-section flexible conductor | 1.5 - 10 mm ² |
| Cross-section rigid conductor | 1 - 6 mm ² |

Power

| | |
|---------------------------|-----|
| Total power loss under IN | 1 W |
|---------------------------|-----|

Dimensions

| | |
|--------|-------|
| Height | 85 mm |
| Width | 70 mm |
| Depth | 64 mm |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Voltage

| | |
|-----------------------------|-------|
| Rated insulation voltage Ui | 690 V |
|-----------------------------|-------|

Equipment

| | |
|--------------|----|
| With battery | No |
|--------------|----|

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |

Illustrations | Drawings

