




EE702



Compact twilight switch enhanced 16A

Technical Features

Voltage

Rated operational voltage U _e	230 - 230 V
--	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

230 V incandescent and halogen lamp	2300 W
-------------------------------------	--------

Settings

Switch off delay time	40 s
Switch on delay time	10 s

Use conditions

Storage/transport temperature	-30 - +60 °C
-------------------------------	--------------

Connection

Cross-section flexible conductor	1 - 4 mm ²
Cross-section rigid conductor	1 - 4 mm ²

Texts

Installation mode	With pipe clamp for mast fixing Installation possible on flush-mounted box For wall and mast assembly
Type of connection	With screw terminals

Electric current

Switching current	10 A
-------------------	------

Dimensions

Height	95 mm
Width	80 mm
Depth	42.50 mm

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes