



HIB425M

**Motorized transfer switch 4P 250A**

**Technical Features**

**Voltage**

Rated operational voltage U<sub>e</sub> 380 - 415 V

**Electric current**

Rated current 250 A

Rated conditional short-circuit current I<sub>cc</sub> with gl-gG fuses 50 kA

**Power**

Rated operational power under 400 V AC AC1 164000 W

**Architecture**

Number of poles 4

Device construction type Fixed built-in

**Compatibility**

Suitable for DIN Rail No

Suitable for distribution board Yes

**Installation, mounting**

Mounting on Mounting plate

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes