



JVC3600S25TW

### 250A TPN board, INVICTA, 36P Chassis, ISO-STD-GR

#### Technical Features

##### Connection

Number of accessible phases	36
-----------------------------	----

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Electric current

Rated current	250 A
Breaking and opening capacity Idm	0 kA

##### Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	Isolator
Number of switches	1
Type of busbar chassis	Fixed load chassis

##### Capacity

Number of modules	16
-------------------	----

##### Dimensions

Height	900 mm
Width	480 mm
Depth	135 mm

##### Cover, door

Door/cover is transparent	No
---------------------------	----

##### Materials

Material	Steel
RAL code	7035
Colour	Light grey

##### Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Key lock With lock

##### Architecture

Number of poles	36
-----------------	----

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes